

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	260330 12/07
GTIN	4062406576899
Item class	21T

Technical description

Head length L_1	25 mm
Centre offset L_3	8 mm
ISO code toolholder	A12L SDQCR/L07
Series	GARANT Master
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Shank $\varnothing D_s$	12 mm
Overall length L	140 mm
Clamping height L_2	11 mm
Minimum pre-drill $\varnothing D_{min}$	15 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

