

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 25/11mm

Order data

Order number	260331 25/11
GTIN	4062406576998
Item class	21T

Technical description

Series	GARANT Master
ISO code toolholder	A25R SDQCR/L11
Minimum pre-drill $\varnothing D_{\min}$	31 mm
Shank $\varnothing D_s$	25 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Overall length L	200 mm
Head length L ₁	40 mm
Clamping height L ₂	23 mm
Centre offset L ₃	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

