

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank  $\varnothing$  / insert size: 20/11mm**

**Order data**

Order number	260330 20/11
GTIN	4062406576929
Item class	21T

**Technical description**

suitable indexable insert	DC.. 11T3..
Clamping height $L_2$	18 mm
Shank $\varnothing D_s$	20 mm
Centre offset $L_3$	13 mm
Minimum pre-drill $\varnothing D_{min}$	25 mm
ISO code toolholder	A20R SDQCR/L11
Series	GARANT Master
Overall length L	200 mm
Pack of insert screws	269028 8
Head length $L_1$	36 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

