

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	260331 16/11
GTIN	4062406576974
Item class	21T

Technical description

suitable indexable insert	DC.. 11T3..
Centre offset L_3	14 mm
Shank $\varnothing D_s$	16 mm
ISO code toolholder	A16Q SDQCR/L11
Overall length L	180 mm
Series	GARANT Master
Minimum pre-drill $\varnothing D_{min}$	23 mm
Head length L_1	28 mm
Clamping height L_2	15 mm
Pack of insert screws	269028 8
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

