

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 20/11mm

Order data

Order number	260331 20/11
GTIN	4062406576981
Item class	21T

Technical description

ISO code toolholder	A20R SDQCR/L11
Head length L_1	36 mm
Shank $\varnothing D_s$	20 mm
Pack of insert screws	269028 8
Minimum pre-drill $\varnothing D_{min}$	25 mm
Clamping height L_2	18 mm
Overall length L	200 mm
suitable indexable insert	DC.. 11T3..
Series	GARANT Master
Centre offset L_3	13 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

