

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank Ø / insert size: 16/07mm

Order data

| | |
|--------------|---------------|
| Order number | 260331 16/07 |
| GTIN | 4062406576967 |
| Item class | 21T |

Technical description

| | |
|-------------------------------|-------------------------------|
| Centre offset L_3 | 10 mm |
| Clamping height L_2 | 15 mm |
| Overall length L | 180 mm |
| suitable indexable insert | DC.. 0702.. |
| Shank Ø D_s | 16 mm |
| Pack of insert screws | 269028 7 |
| ISO code toolholder | A16Q SDQCR/L07 |
| Head length L_1 | 28 mm |
| Series | GARANT Master |
| Minimum pre-drill Ø D_{min} | 19 mm |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 3×D |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

