

**Mitutoyo****External blade micrometer, Measuring range: 25-50mm****Order data**

Order number	421896 25-50
GTIN	4946368847320
Item class	44A

**Description****Version:**

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

**Supplied with:**

From size 25-50 including 1 setting standard.

**Technical description**

Spindle pitch	0.5 mm
Measuring range	25 - 50 mm
Flat blade anvils width	0.75 mm
Flat blade anvils length	6.5 mm
Scale divisions	0.01 mm
Micrometer barrel graduations	1/50 mm
Spindle $\varnothing$	6.35 mm
Calibration	B2
Standard	DIN 863

Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

## Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100