

Mitutoyo**External blade micrometer, Measuring range: 50-75mm****Order data**

Order number	421896 50-75
GTIN	4946368847337
Item class	44A

Description**Version:**

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Flat blade anvils width	0.75 mm
Spindle pitch	0.5 mm
Scale divisions	0.01 mm
Flat blade anvils length	6.5 mm
Spindle Ø	6.35 mm
Calibration	B2
Micrometer barrel graduations	1/50 mm
Measuring range	50 - 75 mm
Standard	DIN 863

Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100