



## Cantilever arm stile KRM double-sided, Height / cantilever arm depth: 2500/600mm



### Order data

Order number	991671 2500/600
GTIN	4052941776847
Item class	95S

### Description

#### Version:

Cantilever arm stile of galvanised steel with 50 mm system holes. Base profiles painted, RAL 5010 Gentian blue, for even distribution of load on the floor. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

#### Suitable for :

Extension of cantilever arm rack KRM No. 991640 – 991653. Cantilever arm depth 600 mm.

#### Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

Height adjustment interval: 50 mm

Height: 2500 mm

Depth: 1440 mm

Load capacity per stand: 1500 kg

### Technical description

Application range	Cantilever arm racking
Depth	1440 mm

Height	2500 mm
Series	KRM
Load capacity per stand	1500 kg
Height adjustment interval	50 mm
Type of product	Racking support