



## Cantilever arm stile KRM single-sided, Height / cantilever arm depth: 2000/400mm



### Order data

Order number	991670 2000/400
GTIN	4052941776663
Item class	95S

### Description

#### Version:

Cantilever arm stile of galvanised steel with 50 mm system holes. Base profiles painted, RAL 5010 Gentian blue, for even distribution of load on the floor. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

#### Suitable for :

Extension of cantilever arm rack KRM No. 991640 – 991653. Cantilever arm depth 400 mm.

#### Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

Height adjustment interval: 50 mm

Height: 2000 mm

Depth: 700 mm

Load capacity per stand: 2300 kg

### Technical description

Application range	Cantilever arm racking
Depth	700 mm

Height	2000 mm
Series	KRM
Load capacity per stand	2300 kg
Height adjustment interval	50 mm
Type of product	Racking support