



Cantilever arm stile KRM single-sided, Height / cantilever arm depth: 2500/600mm



Order data

Order number	991670 2500/600
GTIN	4052941776724
Item class	95S

Description

Version:

Cantilever arm stile of galvanised steel with 50 mm system holes. Base profiles painted, RAL 5010 Gentian blue, for even distribution of load on the floor. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

Suitable for :

Extension of cantilever arm rack KRM No. 991640 – 991653. Cantilever arm depth 600 mm.

Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

Height adjustment interval: 50 mm

Height: 2500 mm

Depth: 900 mm

Load capacity per stand: 1500 kg

Technical description

Depth	900 mm
Height	2500 mm

Application range	Cantilever arm racking
Series	KRM
Load capacity per stand	1500 kg
Height adjustment interval	50 mm
Type of product	Racking support