



Cantilever arm stile KRM single-sided, Height / cantilever arm depth: 3000/800mm



Order data

Order number	991670 3000/800
GTIN	4052941776779
Item class	95S

Description

Version:

Cantilever arm stile of galvanised steel with 50 mm system holes. Base profiles painted, RAL 5010 Gentian blue, for even distribution of load on the floor. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

Suitable for :

Extension of cantilever arm rack KRM No. 991640 – 991653. Cantilever arm depth 800 mm.

Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

Height adjustment interval: 50 mm

Height: 3000 mm

Depth: 1100 mm

Load capacity per stand: 950 kg

Technical description

Application range	Cantilever arm racking
Depth	1100 mm

Height	3000 mm
Series	KRM
Load capacity per stand	950 kg
Height adjustment interval	50 mm
Type of product	Racking support