



Cantilever arm stile KRM double-sided, Height / cantilever arm depth: 2000/500mm



Order data

Order number	991671 2000/500
GTIN	4052941776793
Item class	95S

Description

Version:

Cantilever arm stile of galvanised steel with 50 mm system holes. Base profiles painted, RAL 5010 Gentian blue, for even distribution of load on the floor. 2 longitudinal braces are required in each case to connect cantilever arm stiles.

Suitable for :

Extension of cantilever arm rack KRM No. 991640 – 991653. Cantilever arm depth 500 mm.

Colour:

Cantilever arm stile galvanised, feet and cantilever arms RAL 5010 Gentian blue.

Height adjustment interval: 50 mm

Height: 2000 mm

Depth: 1240 mm

Load capacity per stand: 1900 kg

Technical description

Height	2000 mm
Depth	1240 mm

Application range	Cantilever arm racking
Series	KRM
Load capacity per stand	1900 kg
Height adjustment interval	50 mm
Type of product	Racking support