



## Digital plastic caliper digiMax®, Type: 150D



### Order data

Order number	412830 150D
GTIN	4010995294229
Item class	46P

### Description

#### Version:

Non-metallic high-tech material with 50 % fibre content.

Character height 7.5 mm, 5-character digital display

**Measuring range 0 – 150 mm.**

#### Supplied with:

1 battery No. 081560 size 357.

Packaging: sturdy box

Standard: Manufacturer's standard

Reversible reading: mm / inch

Depth gauge: flat

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Error limit: 0.05 mm

Jaw length: 40 mm

### Technical description

Standard	Manufacturer's standard
Jaw length	40 mm
Measuring range	0 - 150 mm
Digit height LCD display	7.5 mm
Depth gauge	flat
Power supply	Battery-powered

## Data sheet

Depth gauge available	yes
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Number of batteries contained	1
Reversible reading	mm / inch
Error limit	0.05 mm
Article no of the battery / rechargeable battery fitted	081560 357
Measurement technology	digital
Packaging	sturdy box
Type of product	Universal calipers

### Services

Labelling laser-etched Type	018940
-----------------------------	--------

### Accessories

Plastic case Type MS150	412470 MS150
Button cell / special battery Battery type 357	081560 357
Plastic case Type MS150	412468 MS150