



Digital workshop caliper, Measuring range: 300mm



Order data

Order number	415525 300
GTIN	4062406579531
Item class	42A

Description

Version:

Caliper for inside and outside measurements (with preset). Easy-to-read LCD display with extra-large characters. Optimum guidance and sliding characteristics due to **double Vee guides** mounted in plastic. Stainless steel jaws, precision ground. With two movable and **interchangeable jaws. Including measuring force limitation.**

Supplied with:

Incl. 1 battery No. 081560 size CR2032.

Optional extras:

Setting gauge No. 415527 size Set. Measuring jaws with thread M2.5 No. 415526 size 90 with thread M2.5 for special contact points No. 434900 – 434910.

Technical description

Scale divisions	0.01 mm
Scale divisions	0.0005 in
Power supply	Battery-powered
Internal jaw \varnothing	10 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Reversible reading	mm / inch
Weight	0.65 kg
Preset function	yes
Error limit	0.04 mm

Jaw length	90 mm
Number of batteries contained	1
Measuring range	0 - 300 mm
Calibration	A1
Standard	Works standard
Measuring tips	yes
Measurement technology	digital
Material	ABS
all parts	hardened
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------