



## Digital workshop caliper, Measuring range: 1500mm



### Order data

Order number	415525 1500
GTIN	4062406579579
Item class	42A

### Description

#### Version:

Caliper for inside and outside measurements (with preset). Easy-to-read LCD display with extra-large characters. Optimum guidance and sliding characteristics due to **double Vee guides** mounted in plastic. Stainless steel jaws, precision ground. With two movable and **interchangeable jaws. Including measuring force limitation.**

#### Supplied with:

Incl. 1 battery No. 081560 size CR2032.

#### Optional extras:

Setting gauge No. 415527 size Set. Measuring jaws with thread M2.5 No. 415526 size 90 with thread M2.5 for special contact points No. 434900 – 434910.

### Technical description

Preset function	yes
Measuring range	0 - 1500 mm
Power supply	Battery-powered
Weight	2.2 kg
Reversible reading	mm / inch
Article no of the battery / rechargeable battery fitted	081560 CR2032
Error limit	0.1 mm
Calibration	A1
Jaw length	150 mm

Scale divisions	0.0005 in
Scale divisions	0.01 mm
Internal jaw Ø	20 mm
Number of batteries contained	1
Standard	Works standard
Measuring tips	yes
Measurement technology	digital
Material	ABS
all parts	hardened
Type of product	Workshop calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 2000 mm	021000 2000
--	-------------

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------