



## Digital workshop caliper, Measuring range: 3000mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 415525 3000   |
| GTIN         | 4062406579593 |
| Item class   | 42A           |

### Description

#### Version:

Caliper for inside and outside measurements (with preset). Easy-to-read LCD display with extra-large characters. Optimum guidance and sliding characteristics due to **double Vee guides** mounted in plastic. Stainless steel jaws, precision ground. With two movable and **interchangeable jaws. Including measuring force limitation.**

#### Supplied with:

Incl. 1 battery No. 081560 size CR2032.

#### Optional extras:

Setting gauge No. 415527 size Set. Measuring jaws with thread M2.5 No. 415526 size 90 with thread M2.5 for special contact points No. 434900 – 434910.

### Technical description

|                                                         |                 |
|---------------------------------------------------------|-----------------|
| Error limit                                             | 0.25 mm         |
| Power supply                                            | Battery-powered |
| Calibration                                             | A1              |
| Measuring range                                         | 0 - 3000 mm     |
| Reversible reading                                      | mm / inch       |
| Preset function                                         | yes             |
| Weight                                                  | 3.2 kg          |
| Jaw length                                              | 150 mm          |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032   |

|                               |                   |
|-------------------------------|-------------------|
| Scale divisions               | 0.01 mm           |
| Scale divisions               | 0.0005 in         |
| Number of batteries contained | 1                 |
| Internal jaw $\varnothing$    | 20 mm             |
| Standard                      | Works standard    |
| Measuring tips                | yes               |
| Measurement technology        | digital           |
| Material                      | ABS               |
| all parts                     | hardened          |
| Type of product               | Workshop calipers |

## Services

|                                                                    |             |
|--------------------------------------------------------------------|-------------|
| CalibrationCalipers / depth gauges maximum measuring range 3000 mm | 021000 3000 |
|--------------------------------------------------------------------|-------------|

## Accessories

|                                                   |               |
|---------------------------------------------------|---------------|
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |
|---------------------------------------------------|---------------|