

**Mitutoyo**
**Digital depth gauge AOS with data output, Measuring range: 300mm**

**Order data**

Order number	418711 300
GTIN	4946368846460
Item class	44A

**Description**
**Version:**

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cables No. 497080 and 497100.

**Technical description**

Scale divisions	0.01 mm
Calibration	A1
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Bridge length	100 mm
Cross-section measuring beam	16×3.5 mm
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Standard	ISO 13385
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened

Packaging	Wallet
Measurement method of the measuring instrument	electro-magnetic inductive procedure
Type of product	Depth gauge

## Services

DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300