

Mitutoyo**Digital ABS workshop caliper IP67 with nib-style/standard jaws, Measuring range: 300mm****Order data**

Order number	415355 300
GTIN	4946368846316
Item class	44A

Description**Version:**

Measured result is displayed in easy-to-read digits.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497085.

Technical description

IP Index of Protection	IP 67
Measuring range	0 - 300 mm
Article no of the battery / rechargeable battery fitted	081560 357
Internal jaw \varnothing	10 mm
Number of batteries contained	1
Power supply	Battery-powered

Scale divisions	0.01 mm
Calibration	A1
Jaw length	90 mm
Measurement deviation E MPE	± 0.04 mm
Standard	ISO 13385
Interface	USB interface
Interface	USB interface
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300