



Cordless cartridge gun, Type: C18PCG-310



Order data

Order number	083503 C18PCG-310
GTIN	4002395001439
Item class	03L

Description

Version:

- Push rod automatically returns to prevent drips.
- Press-out speed is regulated electronically using a control wheel with 6 speed settings.
- REDLINK™ electronics – overload protection in the machine and battery for a long working life.
- Constant flow of sealant, fewer bubbles and the entire cartridge content is used.
- Optimised for all popular adhesives and sealants, even at cooler temperatures.
- Single-cell monitoring for optimised tool life.

Supplied with:

Supplied with 1 pc. M18 B2 battery pack, 1 pc. M12-18 C charger, tool case.

Technical description

Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Number of rechargeable batteries contained	1
suitable for cartridge size	310 g
Power supply	Rechargeable battery-powered
Battery capacity	2 Ah

Weight including rechargeable battery	2.3 kg
maximum press-out pressure	459 kg
Packaging	Bag
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Grease gun

Accessories

Battery starter set High Output™ Type M18HNRG55	073830 M18HNRG55
Battery starter set Type M18NRG5	073839 M18NRG5
Li-ion battery High Output™ Battery type MHB3	073808 MHB3
Li-ion battery High Output™ Battery type MHB8	073810 MHB8
Battery starter set High Output™ Battery type M18HNRG3	073826 M18HNRG3
Battery starter set High Output™ Type M18HNRG12	073833 M18HNRG12
Li-ion system M18B2 Battery type MB18	073827 MB18
Li-ion battery High Output™ Battery type MHB12	073811 MHB12
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery starter set High Output™ Type M18HNRG8	073831 M18HNRG8
Li-ion battery High Output™ Battery type MHB55	073809 MHB55