

Sideboard with sliding doors, height of 2 box files, Width: 1200mm



Order data

Order number	974211 1200
GTIN	2050002053656
Item class	91Q

Description

Version:

Sliding-door cabinet of wood with centre partition and 2 storage shelves (left and right of the centre partition) 25 mm thick, adjustable at 32 mm intervals. Cabinet with sturdy finished rear panel. Supplied with curved door handles in metal grey. Steel base 30 mm high, always metal grey, including levelling screws. Cylinder lock with 2 keys.

Colour:

Designs available in 5 colours: royal maple, natural oak, light grey, pearl white, metal grey.

Note:

The following designs are only available until 31/07/2023: beech, ash, maple, walnut.

Technical description

Height	779 mm
Width	1200 mm
Surface body	wood
Electronic locking system can be retrofitted	no
Base height	30 mm
Lock numbers individually interchangeable	no
Grip shape	Curved handle

with base	yes
compatible with integrated locking systems	no
Material of the base	Sheet metal
Usable height	699 mm
Depth	450 mm
Number of shelves	2
Version	Sideboard
Height adjustment interval	32 mm
Colour selection	Finish: metal grey, light grey, pearl white, romaple, natural oak
Type of product	Office cabinet