

Electrically height-adjustable office desk, Width: 2000mm



Order data

Order number	974024 2000
GTIN	2050002050785
Item class	91Q

Description

Version:

Office desk with electric height adjustment using controls. Base of powder-coated welded steel frame. Table surface mounted by direct bolting on the frame and two asymmetrically arranged profile bearers. The entire leg area of the frame is clear of obstructions, so mobile drawer units up to 560 mm in height can be accommodated under the desk. Speed of travel for height adjustment 38 mm/s (unloaded). Noise level less than 50 dB. Rail with pad for 10 mm height adjustment. Supplied with approach protection by means of resistance measurement. Melamine desk top with décor surface, 25 mm thick.

Standard:

DIN EN 527-1/-2/-3 für Grundkonstruktion, DIN 60335-1 elektr. Sicherheit.

Colour:

Desk top decoration available in 5 colours: royal maple, natural oak, light grey, pearl white, metal grey.

Base frame available in 3 colours: pure white, aluminum silver, metal grey.

Note:

Due to its strong reflection, the table top in metal grey is not recommended.

The following designs are only available until 31/07/2023: beech, ash, maple, walnut.

Technical description

Height adjustment range	650 - 1300 mm
Worktop thickness	25 mm
Width	2000 mm

maximum load capacity	70 kg
Depth	800 mm
Weight	75 kg
Version	With electric height adjustment
Type of height adjustment	electrical
Insert thickness	25 mm
Colour selection	Metal: Pure white, aluminium silver, metal grey
Colour selection	Finish: metal grey, light grey, pearl white, romaple, natural oak
Type of product	Office desk