

Sideboard with sliding doors, height of 3 box files, Width: 1600mm



Order data

Order number	974212 1600
GTIN	2050002053687
Item class	91Q

Description

Version:

Sliding-door cabinet of wood with centre partition and 2 storage shelves (left and right of the centre partition) 25 mm thick, adjustable at 32 mm intervals. Cabinet with sturdy finished rear panel. Supplied with curved door handles in metal grey. Steel base 30 mm high, always metal grey, including levelling screws. Cylinder lock with 2 keys.

Colour:

Designs available in 5 colours: royal maple, natural oak, light grey, pearl white, metal grey.

Note:

The following designs are only available until 31/07/2023: beech, ash, maple, walnut.

Technical description

Lock numbers individually interchangeable	no
Material of the base	Sheet metal
Height	1163 mm
Number of shelves	4
Usable height	1083 mm
Electronic locking system can be retrofitted	no
compatible with integrated locking systems	no

Depth	450 mm
Grip shape	Curved handle
Surface body	wood
with base	yes
Width	1600 mm
Base height	30 mm
Version	Sideboard
Height adjustment interval	32 mm
Colour selection	Finish: metal grey, light grey, pearl white, romaple, natural oak
Type of product	Office cabinet