

**Small drum extension rack Width 1000 mm, Depth: 500mm**

---

**Order data**

Order number	983210 500
GTIN	4004514227539
Item class	96P

---

**Description****Version:**

T-profile frames and mesh grid shelves, galvanised, mesh 30×30 mm, supporting bar 25×2 mm. With a **maximum shelf load capacity of 150 kg per mesh grid shelf**. Storage shelf levels adjustable at 25-mm intervals. Containment tray height 83 mm (volume of basic rack 37 l / extension rack 34 l). Quick assembly thanks to the simple plug-in design. Can be accessed from both sides.

**Load per bay: 1300 kg.**

**Description:**

Extension size: Nominal depth + 36 mm.

**Application:**

For storage of small drums. Direct drain of escaping liquids due to mesh grid shelves in a tightly welded containment tray.

**Standard:**

Übereinstimmungserklärung gemäß StawaR (Stahlwannenrichtlinie).

**Supplied with:**

4 mesh grid shelves, 1 cover shelf, 1 containment tray.

**Note:**

Additional mesh grid shelves can be found in our eShop under No. 983212 size 500.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

---

## Technical description

Application range	Hazardous substances rack (drums)
Height	2000 mm
Assembled size add-on rack width	1006 mm
Number of shelves	4
Manufacturer's designation	Small drum racks
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Storage	Storage of flammable substances permitted
Storage	Storage of water polluting substances class 1-3
Storage	Storage of environmentally polluting substances
Type of product	Small drum rack

---

## Accessories

Mesh grid shelf Type 500	983212 500
--------------------------	------------