

Garant

**Quick-change boring bar carbide, left-hand, Shank dia. DS / insert size:
8/04mm**


Order data

Order number	268113 8/04
GTIN	4062406583996
Item class	21P

Technical description

Usable depth T	1.1 mm
Shank $\varnothing D_s$	8 mm
Setting angle κ	107.5 degrees
Pack of insert screws	269028 26
Minimum pre-drill $\varnothing D_{min}$	5.2 mm
Insert size	4 mm
suitable indexable insert	DC.. 04T0..
Neck width L_4	4 mm
Overall length L	57 mm
ISO code toolholder	E08X SDQCR/L04
Centre offset L_3	2.6 mm
Head length L_1	26 mm
Standard	DIN 8024
Application type	left-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------