

**Garant**

**Quick-change boring bar carbide, right-hand, Shank  $\varnothing$  DS / insert size: 8/03mm**



## Order data

Order number	268110 8/03
GTIN	4062406583965
Item class	21P

## Technical description

Setting angle $\kappa$	95 degrees
Insert size	3 mm
Pack of insert screws	269028 13
ISO code toolholder	E08X SCLCR/L03
Head length $L_1$	26 mm
Minimum pre-drill $\varnothing D_{\min}$	5 mm
Shank $\varnothing D_s$	8 mm
Overall length $L$	57 mm
Centre offset $L_3$	2.5 mm
Neck width $L_4$	4 mm
suitable indexable insert	CC.. 0301..
Standard	DIN 8024
Application type	right-hand
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

## Accessories

Set of insert screws Type 13

269028 13