

**Garant**

**Quick-change boring bar carbide, right-hand, Shank dia. DS / insert size: 8/04mm**



## Order data

Order number	268112 8/04
GTIN	4062406583989
Item class	21P

## Technical description

Centre offset $L_3$	2.6 mm
Pack of insert screws	269028 26
Insert size	4 mm
Shank $\varnothing D_s$	8 mm
Usable depth T	1.1 mm
ISO code toolholder	E08X SDQCR/L04
Minimum pre-drill $\varnothing D_{min}$	5.2 mm
Setting angle $\kappa$	107.5 degrees
Head length $L_1$	26 mm
Neck width $L_4$	4 mm
suitable indexable insert	DC.. 04T0..
Overall length L	57 mm
Standard	DIN 8024
Application type	right-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------