

Garant
Quick-change boring bar carbide, left-hand, Shank \varnothing DS / insert size: 8/04mm


Order data

Order number	268115 8/04
GTIN	4062406584115
Item class	21P

Technical description

Pack of insert screws	269028 26
Usable depth T	1.5 mm
suitable indexable insert	DC.. 04T0..
Minimum pre-drill $\varnothing D_{\min}$	5.6 mm
Shank $\varnothing D_s$	8 mm
Head length L_1	26 mm
Centre offset L_3	3 mm
Insert size	4 mm
ISO code toolholder	E08X SDUCR/L04
Overall length L	57 mm
Neck width L_4	4 mm
Setting angle κ	93 degrees
Standard	Works standard
Application type	left-hand
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

Set of insert screws Type 26

269028 26