

Garant

Quick-change boring bar carbide, right-hand, Shank \varnothing DS / insert size: 8/04mm


Order data

Order number	268114 8/04
GTIN	4062406584009
Item class	21P

Technical description

Head length L_1	26 mm
ISO code toolholder	E08X SDUCR/L04
Shank \varnothing D_s	8 mm
Setting angle κ	93 degrees
Pack of insert screws	269028 26
Minimum pre-drill \varnothing D_{min}	5.6 mm
Neck width L_4	4 mm
suitable indexable insert	DC.. 04T0..
Usable depth T	1.5 mm
Overall length L	57 mm
Centre offset L_3	3 mm
Insert size	4 mm
Standard	Works standard
Application type	right-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar