

Garant

**Quick-change boring bar carbide, right-hand, Shank dia. DS / insert size:
8/05mm**


Order data

Order number	268118 8/05
GTIN	4062406584146
Item class	21P

Technical description

Usable depth T	3 mm
Head length L ₁	26 mm
Overall length L	57 mm
ISO code toolholder	E08X SVXCR/L05
Shank Ø D _s	8 mm
Setting angle κ	113 degrees
Insert size	5 mm
Minimum pre-drill Ø D _{min}	9.2 mm
Neck width L ₄	6 mm
suitable indexable insert	VC.. 0501..
Centre offset L ₃	5 mm
Pack of insert screws	269028 26
Standard	Works standard
Application type	right-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------