

Garant

**Quick-change boring bar carbide, right-hand, Shank dia. DS / insert size:
8/05mm**



Order data

Order number	268122 8/05
GTIN	4062406584184
Item class	21P

Technical description

Head length L_1	26 mm
Pack of insert screws	269028 26
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Overall length L	57 mm
Neck width L_4	6 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	8 mm
Setting angle κ	95 degrees
suitable indexable insert	VC.. 0501..
Centre offset L_3	5 mm
Insert size	5 mm
ISO code toolholder	E08X SV95CR/L05
Standard	Works standard
Application type	right-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------