

Garant
**Quick-change boring bar carbide, left-hand, Shank dia. DS / insert size:
8/05mm**

Order data

Order number	268123 8/05
GTIN	4062406584191
Item class	21P

Technical description

Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Setting angle κ	95 degrees
suitable indexable insert	VC.. 0501..
Insert size	5 mm
Neck width L_4	6 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	8 mm
Head length L_1	26 mm
ISO code toolholder	E08X SV95CR/L05
Centre offset L_3	5 mm
Overall length L	57 mm
Pack of insert screws	269028 26
Standard	Works standard
Application type	left-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------