

**Garant**

**Quick-change boring bar carbide, left-hand, Shank dia. DS / insert size:  
8/05mm**


**Order data**

Order number	268121 8/05
GTIN	4062406584177
Item class	21P

**Technical description**

Neck width $L_4$	6 mm
Shank $\varnothing D_s$	8 mm
ISO code toolholder	E08X SVLCR/L05
suitable indexable insert	VC.. 0501..
Overall length L	57 mm
Pack of insert screws	269028 26
Usable depth T	3 mm
Centre offset $L_3$	5 mm
Minimum pre-drill $\varnothing D_{min}$	9.2 mm
Head length $L_1$	26 mm
Setting angle $\kappa$	95 degrees
Insert size	5 mm
Standard	Works standard
Application type	left-hand
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------