



ECO knurl forming tool universal, Shank size: 16Xmm



Order data

Order number	290041 16X
GTIN	4030741881190
Item class	29H

Description

Version:

Used conventionally.

Can be used universally as right-hand or left-hand version.

Note:

Tip height must be adjusted.

Technical description

Shank width	16 mm
for knurl width w	8 mm
for knurl $\varnothing d_1$	20 mm
for knurl bore $\varnothing d_2$	6 mm
Working range	10 - 110 mm
Shank height	16 mm
Roller pin	299911 3
Cutting direction	left-hand and right-hand
for knurl profile	RBR 2×BL
for knurl profile	RBL 2×BR
for knurl profile	RAA 2×AA

for knurl profile	RAA 1×AA
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

Accessories

ECO knurl forming tool set Type 16	290050 16
------------------------------------	-----------