



Software option, roughness, Type: PRO



Order data

Order number	499252 PRO
GTIN	4062406581343
Item class	41Q

Description

Version:

Software option for measuring the roughness from a roughness value of Rz 1 or Ra 0.3. Simple and intuitive operation. Determination of roughness, ripple and primary profile. Standard evaluation of all parameters to ISO 4287, ISO 12085, JIS 601 B, ISO 13565 II, ISO10049.

- **Automatic selection of limit wave length of the filter (cut-off) and sampling section to ISO 4288 and ISO 3274.**
- **Evaluation parameters can be provided with tolerance limits and intervention limits on both sides.**
- **Can be retrofitted for devices from build year 11/2020.**

Additionally, evaluation and display of all parameters and graphs to ISO 4287, ISO 12085, JIS 601 B, ISO 13565 II, ISO 10049. Evaluation area can be shifted individually along a sampling section of any desired length (with simultaneous recalculation of all parameters).

Profiles for the evaluation permit (additional) settings of the limit wave length of the filter or changing the type of filter not defined in the standard.

Optional extras:

Roughness probe tips No. 499273 and 499275, roughness standard 499580.

Note:

Technical support and training on request.

Technical description

Series	CM1
--------	-----

Type of product

Software