

Garant UNI LINE**UNI Panel, Type: M****Order data**

Order number	955440 M
GTIN	4062406583293
Item class	9GC

Description**Version:**

Slender folded sheet metal column, double-pannelled with perforated back panel on both sides
□ 9×9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Sturdy base plate in anthracite permits easy set up and movement.

Colour:

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

Note:

ID tags can be found under no. 955443 - 955444. Suitable pictograms (various application purposes) for marking boards can be found under No. 955474.

Technical description

Height	1565 mm
Width	390 mm
Series	Panel
Weight	31 kg
Depth	440 mm

Safe working load	30 kg
Hoffmann perforated panel grid interval	9×9
Type of product	Perforated panel stand