


Garant UNI LINE**UNI Panel, Type: S****Order data**

Order number	955440 S
GTIN	4062406583286
Item class	9GC

Description**Version:**

Slender folded sheet metal column, double-panelled with perforated back panel on both sides
 □ 9×9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Sturdy base plate in anthracite permits easy set up and movement.

Colour:

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

Note:

Marking boards can be found under no. 955442 - 955444. Matching pictograms (for various applications) for marking boards can be found under no. 955474

Hoffmann perforated panel grid interval: 9×9

Height: 1375 mm

Depth: 380 mm

Width: 300 mm

Safe working load: 30 kg

Weight: 17 kg

Technical description

Series	Panel
--------	-------

Depth	380 mm
Width	300 mm
Height	1375 mm
Safe working load	30 kg
Weight	17 kg
Hoffmann perforated panel grid interval	9×9
Type of product	Perforated panel stand