

Garant UNI LINE**UNI Panel, Type: L****Order data**

Order number	955440 L
GTIN	4062406583309
Item class	9GC

**Description****Version:**

Slender folded sheet metal column, double-panelled with perforated back panel on both sides  
 □ 9×9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Sturdy base plate in anthracite permits easy set up and movement.

**Colour:**

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

**Note:**

Marking boards can be found under no. 955442 - 955444. Matching pictograms (for various applications) for marking boards can be found under no. 955474

Hoffmann perforated panel grid interval: 9×9

Height: 2165 mm

Width: 610 mm

Depth: 440 mm

Safe working load: 30 kg

Weight: 45 kg

**Technical description**

Safe working load	30 kg
-------------------	-------

Width	610 mm
Series	Panel
Weight	45 kg
Height	2165 mm
Depth	440 mm
Hoffmann perforated panel grid interval	9×9
Type of product	Perforated panel stand