

Garant UNI LINE**UNI Panel, Type: L****Order data**

|              |               |
|--------------|---------------|
| Order number | 955440 L      |
| GTIN         | 4062406583309 |
| Item class   | 9GC           |

**Description****Version:**

Slender folded sheet metal column, double-panelled with perforated back panel on both sides  
□ 9×9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Sturdy base plate in anthracite permits easy set up and movement.

**Colour:**

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

**Note:**

ID tags can be found under no. 955443 - 955444. Suitable pictograms (various application purposes) for marking boards can be found under No. 955474.

**Technical description**

|                   |         |
|-------------------|---------|
| Safe working load | 30 kg   |
| Width             | 610 mm  |
| Series            | Panel   |
| Weight            | 45 kg   |
| Height            | 2165 mm |

|   |                        |
|---|------------------------|
| Depth                                   | 440 mm                 |
| Hoffmann perforated panel grid interval | 9×9                    |
| Type of product                         | Perforated panel stand |