



Vernier caliper, Measuring range: 1500mm



Order data

Order number	415196 1500
GTIN	4062406584283
Item class	42A

Description

Version:

Vernier and reading face non-glare, satin chromium plated. Measuring faces hardened and ground. **Long jaws for measuring large workpieces and workpiece Ø.** With locking screw. Offset and rounded jaw ends for internal measurements. With fine adjustment.

Technical description

Jaw length	200 mm
Measuring range	0 - 1500 mm
Scale divisions	0.05 mm
Reversible reading	mm / inch
Graduation	1/20 mm
Standard	Works standard
Error limit	0.36 mm
Internal jaw Ø	30 mm
Calibration	A1
Weight	5.3 kg
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX

all parts	hardened
Type of product	Workshop calipers
Services	
CalibrationCalipers / depth gauges maximum measuring range 2000 mm	021000 2000