



Vernier caliper, Measuring range: 300mm



Order data

Order number	415196 300
GTIN	4062406584245
Item class	42A

Description

Version:

Vernier and reading face non-glare, satin chromium plated. Measuring faces hardened and ground. **Long jaws for measuring large workpieces and workpiece Ø.** With locking screw. Offset and rounded jaw ends for internal measurements.

Technical description

Measuring range	0 - 300 mm
Weight	0.44 kg
Calibration	A1
Reversible reading	mm / inch
Internal jaw Ø	10 mm
Graduation	1/20 mm
Scale divisions	0.05 mm
Standard	Works standard
Jaw length	90 mm
Error limit	0.05 mm
Vernier graduations mm/inch	yes
Measurement technology	analogue

Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300