



## Vernier caliper, Measuring range: 500mm



### Order data

Order number	415196 500
GTIN	4062406584252
Item class	42A

### Description

#### Version:

Vernier and reading face non-glare, satin chromium plated. Measuring faces hardened and ground. **Long jaws for measuring large workpieces and workpiece Ø.** With locking screw. Offset and rounded jaw ends for internal measurements.

### Technical description

Error limit	0.07 mm
Calibration	A1
Internal jaw Ø	20 mm
Reversible reading	mm / inch
Graduation	1/20 mm
Standard	Works standard
Scale divisions	0.05 mm
Weight	1.1 kg
Jaw length	150 mm
Measuring range	0 - 500 mm
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX

all parts	hardened
Type of product	Workshop calipers

**Services**

DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500
CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500