



Vernier caliper, Measuring range: 800mm



Order data

Order number	415196 800
GTIN	4062406584269
Item class	42A

Description

Version:

Vernier and reading face non-glare, satin chromium plated. Measuring faces hardened and ground. **Long jaws for measuring large workpieces and workpiece Ø.** With locking screw. Offset and rounded jaw ends for internal measurements.

Technical description

Calibration	A1
Graduation	1/20 mm
Jaw length	150 mm
Standard	Works standard
Reversible reading	mm / inch
Scale divisions	0.05 mm
Error limit	0.1 mm
Weight	2.1 kg
Internal jaw Ø	20 mm
Measuring range	0 - 800 mm
Vernier graduations mm/inch	yes
Measurement technology	analogue
Material	Stainless steel, INOX

all parts	hardened
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000
CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000