

Garant UNI LINE**Set of wheels for UNI Line, 4 pieces, Type: 1****Order data**

Order number	955459 1
GTIN	4062406584702
Item class	9GC

Description**Version:**

Wheels with \varnothing 125 mm. Also ideal for uneven ground. Fibre shields prevent the castors jamming. Optimum smooth running characteristics thanks to high-quality ball bearings. With treadless polyurethane tyres, minimal rolling resistance and low noise. Load capacity per wheel 200 kg. Maximum load capacity when using 4 wheels: 600 kg.

Supplied with:

2 castors and 2 castors with brakes for the wheels and the castor head. Fastening material.

Colour:

Galvanized, not configurable.

Technical description

Load capacity per piece	200 kg
Height	150 mm
Construction height	150 mm
Wheel \varnothing	125 mm
Type of product	Wheel

