

Garant UNILINE

UNI Tower mobile U-shape, Type: M**Order data**

Order number	955465 M
GTIN	4062406586218
Item class	9GC

Description**Version:**

Modular provision system for direct access to work materials and quick visualisation of information. Freely configurable due to a wide variety of accessories and perfect compatibility with the Easyfix system.

All sides, inside and outside with perforated panels $\square 9 \times 9$ mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. U-shape: 2 side walls with rear panel. Can be fitted with drawers and door.

Supplied with:

UNI Tower No. 955462 size M; 2 storage shelves No. 955481 size M; attachment No. 955475 size GREY; push handle No. 955496 size 1.

With 4 castors, \varnothing 125 mm, 2 with parking brake.

Colour:

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

Note:

Further accessories such as pictograms, storage shelves, drawers and doors can be found under No. 955474 – 955499.

Technical description

Safe working load	150 kg
Height	2290 mm
Usable width	540 mm
Weight	105 kg
Wheel Ø	125 mm
Width	720 mm
Depth	750 mm
Usable depth	510 mm
Series	Tower
Shelf load capacity / maximum distributed shelf load (on metal)	100
Hoffmann perforated panel grid interval	9×9
Height adjustment interval	37
Type of product	Perforated panel tower

Accessories

UNI Line push handle Type 1	955496 1
UNI Towermobile U-shape Type M	955462 M
Attachment for UNI Tower M Type GREY	955475 GREY
Set of wheels for UNI Line, 4 pieces Type 1	955459 1
UNI Towerstationary U-shape Type M	955460 M