



Clamp toolholder, right-hand, Type: 3



Order data

Order number	269991 3
GTIN	4960664603220
Item class	250

Description

Clamp toolholder 3 ISO code toolholder: SDJCR1010JX-11FF

suitable indexable insert: DC..11T3..

Functional width L_4 : 10 mm

Head length L_1 : 20 mm

Overall length L: 120 mm

Technical description

Insert size	11 mm
Overall length L	120 mm
Series	QuickTurn
Head length L_1	20 mm
Shank size	10 mm
Functional width L_4	10 mm
ISO code toolholder	SDJCR1010JX-11FF
suitable indexable insert	DC..11T3..
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	no
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Clamp toolholder
-----------------	------------------

Accessories

Screw BH6X25 Type 1	269993 1
Spring SP-6 Type 1	269994 1
Terminal Type 1	269992 1
Clamping screw	229715