

## Garant

### Burr set GARANT Master Uni – medium, 5 pieces, Carbide TiAlN, Number of burrs: 5



#### Order data

Order number	541406 5
GTIN	4062406587079
Item class	51D

#### Description

##### Version:

##### Multi Cut carbide burr set with popular shape variants.

The newly developed innovative tooth geometry permits a **high metal removal rate** and at the same time **extremely smooth running and very good guidance**. The optimum chip formation (no pointed chips) achieves high surface quality in roughing and finishing applications.

- **for general purpose use.**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAlN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty).

- **Longer tool life.**
- **Less heat input.**
- **Better chip evacuation.**

##### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Supplied with:**

1 pc. each No. 540222 size A0616, C0616, D0807; G0618; M1020.

**Note:**

Materials with poor heat conductivity; reduce speed to avoid overheating of the burr and smearing.

---

**Technical description**

Series	GARANT Master Uni
Tool material	Carbide TiAlN
Shank Ø	6 mm
Number of burrs	5
Type of product	Burr

---

**Accessories**

Burr, coatedGARANT Master Uni – medium Type D0807	540222 D0807
Burr, coatedGARANT Master Uni – medium Type A0616	540222 A0616
Burr, coatedGARANT Master Uni – medium Type G0618	540222 G0618
Burr, coatedGARANT Master Uni – medium Type M1020	540222 M1020
Burr, coatedGARANT Master Uni – medium Type C0616	540222 C0616