

## Garant

**Burr set GARANT Master Uni – medium, 8 pieces, Carbide, Number of burrs: 8**



### Order data

Order number	541410 8
GTIN	4062406587086
Item class	51D

### Description

#### Version:

**Multi Cut carbide burr set with popular shape variants.**

The newly developed innovative tooth geometry permits a **high metal removal rate** and at the same time **extremely smooth running and very good guidance**. The optimum chip formation (no pointed chips) achieves high surface quality in roughing and finishing applications.

- **High rate of material removal.**
- **Smooth running.**
- **Low thermal stress, long tool life, improved chip evacuation.**
- **For general-purpose use on steel, stainless steel, aluminium.**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Supplied with:**

1 pc. each No. 540220 size A0616; A1020; C0616; C1020; D0605; D1009; G0618; M1020.

**Note:**

Materials with poor heat conductivity; reduce speed to avoid overheating of the burr and smearing.

---

**Technical description**

Series	GARANT Master Uni
Tool material	Carbide
Shank Ø	6 mm
Number of burrs	8
Type of product	Burr

---

**Accessories**

BurrGARANT Master Uni – medium Type G0618	540220 G0618
BurrGARANT Master Uni – medium Type D0605	540220 D0605
BurrGARANT Master Uni – medium Type M1020	540220 M1020
BurrGARANT Master Uni – medium Type D1009	540220 D1009
BurrGARANT Master Uni – medium Type A1020	540220 A1020
BurrGARANT Master Uni – medium Type C1020	540220 C1020
BurrGARANT Master Uni – medium Type C0616	540220 C0616
BurrGARANT Master Uni – medium Type A0616	540220 A0616