



## Thread "No Go" plug gauge for MultiCheck Digital, Threads: M18



### Order data

Order number	486516 M18
GTIN	4046122621163
Item class	48B

### Description

#### Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

#### Suitable for:

Base unit 486511 size 12-20, measuring sleeve No. 486512 size 12-20 and protective sleeve No. 486515 size, M12 up to M20.

### Technical description

Thread pitch	2.5 mm
Standard	DIN 13
Thread	M18
Type of gauge	"Go" plug gauge
Thread type	M
Test certificate	Manufacturer's test certificate
Calibration	Price on request
Type of product	Thread NoGo plug gauge

### Services

Calibration "Go" / "No Go" thread plug gauge maximum $\varnothing$ 60 mm	028500 60
--	-----------

DAkKS calibration "Go" / "No Go" thread plug gauge  
maximum  $\varnothing$  90 mm

028540 90