



Thread "No Go" plug gauge for MultiCheck Digital, Threads: M2



Order data

Order number	486516 M2
GTIN	4046122621170
Item class	48B

Description

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Suitable for:

Base unit 486511 size 2-10, measuring sleeve No. 486512 size 2-10 and protective sleeve No. 486515 size, M2 up to M10.

Technical description

Standard	DIN 13
Thread pitch	0.45 mm
Thread	M2
Thread type	M
Type of gauge	"No Go" gauge
Test certificate	Manufacturer's test certificate
Calibration	Price on request
Type of product	Thread NoGo plug gauge

Services

Calibration "Go" / "No Go" thread plug gauge maximum \varnothing 60 mm	028500 60
--------------------------------------------------------------------------	-----------

DAkKS calibration "Go" / "No Go" thread plug gauge
maximum \varnothing 90 mm

028540 90